




Insert Part Number		3332-1/2TW
Reference Number		319-8
Internal Thread Form		UNC
Internal Thread Size		1/2-13
Internal Thread Class		2B
External Thread Size		5/8-11
External Thread Class		2B
Drill Size	inch	37/64
Tap Size		5/8-11
Installation Tool		3300-7

Bondsert inserts have external threads of standard size and pitch so no special drills, taps or installation tools are required. Bondsert inserts will not back out or vibrate loose after installation. Immediately upon installation, micro-encapsulated adhesive will begin to set, and a mating fastener can be installed within minutes. The adhesive also seals against liquids and gases to pressures of 6,000psi, and bonds to most metals. To remove an insert, a standard screw extractor can be used, and removal is just a matter of defeating the resistance to torque-out of the thread locking adhesive.

**IMPORTANT** The success of any drilling and tapping operation is dependent upon many factors - type of material being cut, cutting speed, coolant, equipment being used - and it is not possible to give specific drill sizes for each material. Drill sizes shown are recommendations only and Crossroad Distributor Source would strongly encourage testing be performed for specific and critical applications.

# powercoil.com.au

PowerCoil and Loksert are registered trademarks of Bordo International Pty Ltd Australia



INSERT DIMENSIONAL CHARACTERISTICS		
A Mod Minor Diameter	inch	.553 - .557
B Mod Major Diameter	inch	.619 - .623
Insert Length	inch	0.62
Minimum Full Thread Depth	inch	0.68

Tolerances +/- 0.010"

INSERT MATERIAL CHARACTERISTICS		
Brinell Hardness	HB	163
Tensile Strength	PSI	78300

**NOTE** The Thin Wall design requires a modified external thread. While the external thread pitch is standard, the minor diameter is larger than normal. So standard drill/tap combination does not apply. Preparing the hole for installation requires an oversize drill. For example, if a Thin Wall with a 5/8-11 external thread is being installed, a standard 37/64 drill is used as opposed to the typical 17/32, and tapped with a standard 5/8-11 tap.